

Product data sheet

Specifications



Polyester rear part of PLS box 27x36x13.5cm

NSYFPLS2736

⚠ Discontinued on: Dec 2, 2020

⚠ End-of-service on: Dec 31, 2020

⚠ Discontinued

Main

Range	Thalassa
Product Name	Thalassa PLS
Device Short Name	PLS
Enclosure Type	Multi-purpose
Category	Insulating modular rear
Nominal Height	10.63 in (270 mm)
Nominal Width	14.17 in (360 mm)
Nominal Depth	5.31 in (135 mm)
Enclosure Mounting	Wall mounted
Device Composition	1 rear part on enclosure
Body Type	One piece moulded
Type Of Front Cover	Without

Complementary

Material	polyester reinforced with fibreglass
Color	Body Gray RAL 7032)
Standards	NEMA 4X NEMA classification 13 IEC 62208
Product Certifications	UL

Environment

Electrical Insulation Class	Class II
Ip Degree Of Protection	IP65 IEC 60529
Ik Degree Of Protection	IK09 IEC 62262
Fire Resistance	1760 °F (960 °C) IEC 62208
Ambient Air Temperature For Storage	-22...248 °F (-30...120 °C)

Ordering and shipping details

Category	80036-ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
Gtin	3606480188527

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	No
Country Of Origin	ES

Contractual warranty

Warranty	18 months
----------	-----------