

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 87.87 USD

NSYFPLS5454 has not been replaced. Please contact your customer care center for more information.



ⓘ Discontinued

### Main

Range	Thalassa
Product name	Thalassa PLS
Device short name	PLS
Enclosure type	Multi-purpose
Category	Insulating modular rear
Nominal height	21.26 in (540 mm)
Nominal width	21.26 in (540 mm)
Nominal depth	5.31 in (135 mm)
Enclosure mounting	Wall mounted
Device composition	Rear part 1 on enclosure
Body type	One piece moulded
Type of front cover	Without

### Complementary

Material	Polyester reinforced with fibreglass
Colour	Grey RAL 7032 body
Standards	NEMA 4X IEC 62208 NEMA classification 13
Product certifications	UL

### Environment

Electrical insulation class	Class II
IP degree of protection	IP65 IEC 60529
IK degree of protection	IK09 IEC 62262
Fire resistance	1760 °F (960 °C) IEC 62208
Ambient air temperature for storage	-22...248 °F (-30...120 °C)

## Ordering and shipping details

Category	80036 - ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
Nbr. of units in pkg.	1
Package weight(Lbs)	8.1400000000000006
Returnability	N
Country of origin	ES

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------