



19" 2 U partial fixed slides - Fixing onto 19" front uprights - 15 kg load

NSYGB140

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 36.97 USD

Main

Range Of Product	Actassi
Product Or Component Type	Fixed slide
Device Application	Electronic application Multi-purpose
Quantity Per Set	Set of 1

Complementary

Range Compatibility	Actassi VDA Actassi VDS
Material	steel
Surface Finish	Zinc coated
Mounting Support	19" rack, front or rear
Product Compatibility	Spacial SF-S, SF-E, VDM, PLA enclosures
Device Composition	fixing elements 2 rails
Fixing Mode	By clips 19" uprights of rack
Number Of Rack Unit	2U
Permanent Permissible Load	33.07 lb(US) (15 kg)
Thickness	0.05 in (1.2 mm)
Number Of Units 19"	2
Height	3.50 in (88.9 mm)
Width	5.51 in (140 mm)
Depth	1.73 in (44 mm)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480066757
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1 PCE

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	3.15 in (8.0 cm)
Package 1 Width	2.17 in (5.5 cm)
Package 1 Length	5.51 in (14.0 cm)
Package 1 Weight	11.29 oz (320.0 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations