

Product data sheet

Specifications



Fluorescent compact lamp, 11W, 220V, 50/60Hz, socket UTE, type french

NSYLAMCF

⚠ Discontinued on: Jan 23, 2021

⚠ Discontinued

Main

Range Of Product	Lighting and power sockets
Accessory / Separate Part Category	Lighting accessory
Product Or Component Type	Lamp
Device Application	Multi-purpose
Device Composition	fixing elements lamp switch and power socket

Complementary

Outlet Standard	French
Rated Lamp Wattage	11 W
[Ue] Rated Operational Voltage	230 V 50/60 Hz
Bulb Base	2G7
Bulb Type	Fluorescent
Control Type	Built-it switch
Luminous Flux	900 lm
Service Life In Hours	8000 h
Electrical Connection	Screw connector <= 2.5 mm²
Mounting Location	Top front of enclosure
Mounting Support	DIN rail Cross rails Upright Metal parts
Fixing Mode	Clip-in Magnetic fixing Screws
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Thalassa Thalassa PLA Thalassa Thalassa PLM Spacial Spacial SFX Spacial Spacial SMX Spacial Spacial SF Spacial Spacial SM
Material	Light gray plastic
Height	1.57 in (40 mm)
Width	14.65 in (372 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	2.48 in (63 mm)
-------	-----------------

Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529
Electrical Insulation Class	Class I
Flame Retardance	V0 conforming to UL 94
Electromagnetic Compatibility	Emission standard for industrial environments IEC 61000-6-4
Standards	UL 508 A
Product Certifications	VDE
Ambient Air Temperature For Operation	3...149 °F (-16...65 °C)
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)

Ordering and shipping details

Category	80036-ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
Gtin	00785901977070
Returnability	No
Country Of Origin	CN

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------