# Product data sheet

Specifications





# Insulating mounting plate for enclosure H400xW300mm made of bakelite

NSYMB43

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Price\*: 22.21 USD

### Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure Nominal Dimensions	- H: 15.75 in (400 mm) W: 11.81 in (300 mm) - H: 11.81 in (300 mm) W: 15.75 in (400 mm)
Mounting Location	Direct fixing on backstuds Step slide
Mounting Plate Description	Plain
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X
Quantity Per Set	Set of 1
Material	bakelite
Color	Black RAL 9005)

#### Complementary

Fixing Mode	Screwed on backstuds M8 By fixing element
Permanent Permissible Load	66.14 lb(US) (30 kg)
Height	12.80 in (325 mm)
Width	9.84 in (250 mm)
Thickness	0.16 in (4 mm)
Net Weight	11.02 lb(US) (5 kg)

### Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480182723
Returnability	No
Country Of Origin	ES

# **Packing Units**

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.20 in (0.500 cm)
Package 1 Width	9.84 in (25.000 cm)
Package 1 Length	14.37 in (36.500 cm)
Package 1 Weight	19.40 oz (550.000 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	20
Package 2 Height	11.81 in (30 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	25.18 lb(US) (11.420 kg)
Unit Type Of Package 3	P12
Number Of Units In Package 3	160
Package 3 Height	17.72 in (45.000 cm)
Package 3 Width	31.50 in (80.000 cm)
Package 3 Length	47.24 in (120.000 cm)
Package 3 Weight	227.87 lb(US) (103.360 kg)

# **Contractual warranty**

Warranty

18 months

# Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations