

Product data sheet

Specifications



metallic floor-fixing frame for vers.PLAZ or PLAZT W1250xD320mm

NSYMFPLAZ123

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	Thalassa
Accessory / Separate Part Category	Fixing accessory
Product Or Component Type	Floor-fixing frame
Device Application	Multi-purpose
Enclosure Nominal Dimensions	- W: 49.21 in (1250 mm) D: 12.60 in (320 mm)
Mounting Location	On the floor
Range Compatibility	Thalassa Thalassa PLA
Device Composition	fixing elements 4 floor-fixing stud 1 floor-fixing frame

Complementary

Material	steel
Surface Finish	Zinc coated
Fixing Mode	Screwed - on enclosure By floor-fixing studs - on floor
Height	0.31 in (8 mm)
Width	48.43 in (1230 mm)
Depth	10.24 in (260 mm)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480193408
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.13 in (10.5 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	14.37 in (36.5 cm)
Package 1 Length	48.62 in (123.5 cm)
Package 1 Weight	24.25 lb(US) (11.0 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations