Product data sheet

Specifications



Spacial SF intermediate crossbar - enclosure width: 800 mm

NSYMIC8

U To be discontinued on: Sep 30, 2024

① To be discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 331.50 USD

Main

Range	Spacial
Product Or Component Type	Intermediate crossbar
Application	Compartmentalised application
Nominal Dimensions Of The Housing	- W: 31.50 in (800 mm)
Mounting Location	Front of enclosure
Range Compatibility	Spacial SF compartimentalised version
Device Composition	Fixing elements 2 x crossbar

Complementary

Material	steel
Color	Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Fixing Mode	By fixing element - on structure
Adjustment	Adjustable in height every 25 mm
Width	Nominal 31.50 in (800 mm) Real 29.92 in (760 mm)
Depth	2.56 in (65 mm)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480065583
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.95 in (7.5 cm)
Package 1 Width	3.94 in (10.0 cm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 1 Length	31.50 in (80.0 cm)
Package 1 Weight	7.77 lb(US) (3.524 kg)
Unit Type Of Package 2	РАМ
Number Of Units In Package 2	50
Package 2 Height	19.69 in (50.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	423.29 lb(US) (192.0 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations