# **Product data sheet**

Specifications





Plain mounting plate, PanelSeT SFN, Spacial SF, Spacial SM, for electrical enclosure H1200 W800mm, galvanized steel

NSYMP128

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 132.24 USD

#### Main

Range	Spacial	
Accessory / Separate Part Category	Mounting accessory	
Product Or Component Type	Mounting plate	
Device Application	Multi-purpose	
Enclosure Nominal Dimensions	- H: 47.24 in (1200 mm) W: 31.50 in (800 mm)	
Mounting Plate Description	Plain	
Range Compatibility	Spacial Spacial SF Spacial Spacial SM Spacial Spacial SFX Spacial Spacial SMX	
Device Composition	1 mounting plate 2 sliding shoes	
Quantity Per Set	Set of 1	
Material	galvanised steel	

### Complementary

Fixing Mode	By fixing brackets
Maximum Load	300 kg/m²
Permanent Permissible Load	1102.31 lb(US) (500 kg) intermediate position 1322.77 lb(US) (600 kg) back of the enclosure
Height	Fixing centers 41.34 in (1050 mm)  Nominal 47.24 in (1200 mm)  Real 43.19 in (1097 mm)
Width	Nominal 31.50 in (800 mm) Fixing centers 25.59 in (650 mm) Real 27.40 in (696 mm)
Depth	1.06 in (27 mm)

### Ordering and shipping details

Category	US10ES180035
Discount Schedule	0ES1
Gtin	3606485126777
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin

## **Packing Units**

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.38 in (3.5 cm)
Package 1 Width	27.76 in (70.5 cm)
Package 1 Length	43.70 in (111.0 cm)
Package 1 Weight	39.68 lb(US) (18.0 kg)
Unit Type Of Package 2	P12
Number Of Units In Package 2	20
Package 2 Height	29.13 in (74.0 cm)
Package 2 Width	31.50 in (80.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	822.32 lb(US) (373.0 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>Ø</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations