# **Product data sheet**

Specifications





# Spacial SF single ventilated door - 2200x800 mm

NSYPCVD228

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 1,173.43 USD

#### Main

Range	PanelSeT
	Falleloe I
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	19" door
Application	Electronic application
For Enclosure Nominal Dimensions	-
Mounting Location	Front
Range Compatibility	PanelSeT PanelSeT SF
Device Composition	1 door 1 lock with handle and 5 mm double bar insert 1 locking bar system 4 points
Quantity Per Set	Set of 1

## Complementary

Material	sheet steel
Color	Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Lock Type	Lock 5 mm double bar
Number Of Locks	1
Door Type	Fully Ventilated
Door Opening Side	Reversible 120 °)
Height	Nominal 86.61 in (2200 mm)
Width	Nominal 31.50 in (800 mm)

## Ordering and shipping details

Category	US10ES180035
Discount Schedule	0ES1
Gtin	3606480066696
Returnability	No
Country Of Origin	FR

### **Packing Units**

Unit Type Of Package 1 PCE

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	2.76 in (7.0 cm)
Package 1 Width	30.51 in (77.5 cm)
Package 1 Length	90.35 in (229.5 cm)
Package 1 Weight	50.71 lb(US) (23.0 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	10
Package 2 Height	30.31 in (77.0 cm)
Package 2 Width	90.55 in (230.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	577.61 lb(US) (262.0 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations