Product data sheet

Specification





Internal door for Spacial WM encl. H400xW300 steel, RAL7035.Adjustable in depth

NSYPIN43

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 112.98 USD

Main

Range	Spacial	
Accessory / Separate Part Category	Enclosure accessory	
Product Or Component Type	Door	
Application	Multi-purpose	
For Enclosure Nominal Dimensions	-	
Mounting Location	Front side Step slide	
Range Compatibility	Spacial Spacial CRN Spacial Spacial S3D Spacial Spacial S3X	
Device Composition	1 door 4 fixing brackets 2 mounting uprights	

Complementary

Material	Door sheet steel	
Color	All faces Gray RAL 7035)	
Surface Finish	Polyester powder	
Lock Type	Lock 3 mm double bar	
Number Of Locks	1	
Adjustment	Pitch 25 mm (on step slides)	
Door Type	Internal plain	
Door Opening Side	Reversible	
Maximum Load	30 kg/m²	
Height	Nominal: 15.75 in (400 mm)	
Width	Nominal: 11.81 in (300 mm)	
Net Weight	3.53 lb(US) (1.6 kg)	

Ordering and shipping details

Category	US10ES180036	
Discount Schedule	0ES1	
Gtin	3606480168574	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	No	
Country Of Origin	ES	

Packing Units

•		
Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	1.97 in (5.000 cm)	
Package 1 Width	10.43 in (26.500 cm)	
Package 1 Length	15.35 in (39.000 cm)	
Package 1 Weight	3.60 lb(US) (1.633 kg)	
Unit Type Of Package 2	S04	
Number Of Units In Package 2	7	
Package 2 Height	11.81 in (30.000 cm)	
Package 2 Width	15.75 in (40.000 cm)	
Package 2 Length	23.62 in (60.000 cm)	
Package 2 Weight	26.63 lb(US) (12.081 kg)	
Unit Type Of Package 3	P12	
Number Of Units In Package 3	56	
Package 3 Height	35.43 in (90.000 cm)	
Package 3 Width	31.50 in (80.000 cm)	
Package 3 Length	47.24 in (120.000 cm)	
Package 3 Weight	239.53 lb(US) (108.648 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	No need of specific recycling operations	