



Price\* : 1,240.48 USD



## Main

|                           |  |
|---------------------------|--|
| Range                     | Thalassa   |
| Product name              | Thalassa PLA   |
| Enclosure type            | Multi-purpose  |
| Product or component type | Suitable enclosure   |
| Version                   | PLA  |
| Nominal height            | 39.37 in (1000 mm)   |
| Nominal width             | 39.37 in (1000 mm)   |
| Nominal depth             | 12.6 in (320 mm)   |
| Enclosure mounting        | Floor-standing   |
| Device composition        | 1 top part<br>1 bottom part<br>2 rear panel<br>2 door<br>2 side part |

## Complementary

|                             |  |
|-----------------------------|--|
| Body type                   | Sealed top and bottom part assembled with side parts |
| Door type                   | Transparent front                                    |
| Number of doors             | 2  |
| Door opening side           | Right and left 120 °                                 |
| Lock type                   | 4 points lock, 5 mm double-bar                       |
| Accessibility for operation | Rear<br>Front  |
| Removable parts             | Door by hinges<br>Rear panel by fixing element       |
| Material                    | Polyester reinforced with fibreglass                 |
| Colour                      | Grey RAL 7035  |
| Standards                   | UL 508 A   |

|                           |  |
|---------------------------|--|
|                           | IEC 62208                              |
| NEMA degree of protection | NEMA 1<br>NEMA 13<br>NEMA 2<br>NEMA 12 |
| Product certifications    | Veritas<br>UL/cUL listed<br>DNV Marine |

## Environment

|                                     |                                  |
|-------------------------------------|----------------------------------|
| IP degree of protection             | IP65 completely sealed IEC 60529 |
| IK degree of protection             | IK08 glazed door IEC 62262       |
| Fire resistance                     | 1760 °F (960 °C) IEC 62208       |
| Ambient air temperature for storage | -31...194 °F (-35...90 °C)       |

## Ordering and shipping details

|                       |  |
|-----------------------|--|
| Category              | 80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL |
| Discount Schedule     | ES1  |
| GTIN                  | 003606480774362                            |
| Nbr. of units in pkg. | 1  |
| Package weight(Lbs)   | 5.999999999999998E-2                       |
| Returnability         | N  |
| Country of origin     | ES   |

## Offer Sustainability

|                                  |  |
|----------------------------------|--|
| Sustainable offer status         | Green Premium product  |
| RoHS (date code: YYWW)           | Compliant<br><a href="#">Schneider Electric declaration of conformity</a>  |
| REACH                            | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a> |
| Product environmental profile    | Available  |
| Product end of life instructions | Need no specific recycling operations  |