Product data sheet

Specifications





Floor standing polyester enclosure, Thalassa PLA, plain door, ventilated canopy, 1500x1250x320mm, IP44, IK10

NSYPLAT15123G

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 2,151.96 USD

Main

Range	Thalassa
Product Name	Thalassa PLA
Enclosure Type	Multi-purpose
Product Or Component Type	Suitable enclosure
Version	PLAT
Nominal Height	59.06 in (1500 mm)
Nominal Width	49.21 in (1250 mm)
Nominal Depth	12.60 in (320 mm)
Enclosure Mounting	Floor-standing
Device Composition	1 top part 1 bottom part 2 side part 2 door 2 rear panel 1 canopy

Complementary

Open top and sealed bottom part assembled with side parts
Solid front
2
Right and left 120 °)
4 points lock, handle with 5 mm double bar insert
Rear Front Top
Door by hinges Rear panel by fixing element Canopy by fixing element
polyester reinforced with fibreglass
Gray RAL 7035)
IEC 62208
Veritas
Class II

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Environment

Ip Degree Of Protection	IP44 IEC 60529 with ventilated canopy)
Ik Degree Of Protection	IK10 IEC 62262 plain door)
Fire Resistance	1760 °F (960 °C) IEC 62208
Ambient Air Temperature For Storage	-31194 °F (-3590 °C)

Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480775338
Returnability	No
Country Of Origin	ES

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	59.84 in (152.0 cm)
Package 1 Width	15.35 in (39.0 cm)
Package 1 Length	50.00 in (127.0 cm)
Package 1 Weight	168.65 lb(US) (76.5 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	2
Package 2 Height	52.36 in (133 cm)
Package 2 Width	39.37 in (100 cm)
Package 2 Length	65.35 in (166 cm)
Package 2 Weight	390.22 lb(US) (177 kg)

Package 2 Weight

390.22 lb(US) (177 kg)

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations