



Main

Range	Thalassa
Product name	Thalassa PLA
Enclosure type	Multi-purpose
Product or component type	Suitable enclosure
Version	PLAZ
Nominal height	39.37 in (1000 mm)
Nominal width	49.21 in (1250 mm)
Nominal depth	16.54 in (420 mm)
Enclosure mounting	Floor-standing
Device composition	1 top part 1 bottom part 2 rear panel 2 door 1 plinth 2 side part

Complementary

Body type	Sealed top and open bottom part assembled with side parts
Door type	Plain front
Number of doors	2
Door opening side	Right and left 120 °
Lock type	4 points lock, handle with 5 mm double bar insert
Accessibility for operation	Front Rear Bottom
Removable parts	Door by hinges Rear panel by fixing element
Material	Polyester reinforced with fibreglass
Colour	Grey RAL 7035

Standards	IEC 62208
Product certifications	Veritas

Environment

IP degree of protection	IP54 plinth type open bottom IEC 60529
IK degree of protection	IK10 plain door IEC 62262
Fire resistance	1760 °F (960 °C) IEC 62208
Ambient air temperature for storage	-31...194 °F (-35...90 °C)

Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	003606480775581
Nbr. of units in pkg.	1
Package weight(Lbs)	59.539999999999999
Returnability	N
Country of origin	ES

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations