# **Product data sheet**

Specifications





Floor standing polyester enclosure, Thalassa PLA, plain door, open bottom, 750x1250x420mm, IP54, IK10

NSYPLAZ7124G

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 2,090.52 USD

#### Main

Range	Thalassa
Product Name	Thalassa PLA
Enclosure Type	Multi-purpose
Product Or Component Type	Suitable enclosure
Version	PLAZ
Nominal Height	29.53 in (750 mm)
Nominal Width	49.21 in (1250 mm)
Nominal Depth	16.54 in (420 mm)
Enclosure Mounting	Floor-standing
Device Composition	1 top part 1 bottom part 2 side part 2 door 2 rear panel 1 plinth

### Complementary

Body Type	Sealed top and open bottom part assembled with side parts
Door Type	Solid front
Number Of Doors	2
Door Opening Side	Right and left 120 °)
Lock Type	2 points handle lock, 5 mm double-bar
Accessibility For Operation	Bottom Front Rear
Removable Parts	Door by hinges Rear panel by fixing element
Material	polyester reinforced with fibreglass
Color	Gray RAL 7035)
Standards	IEC 62208
Product Certifications	Veritas
Electrical Insulation Class	Class II

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

### **Environment**

Ip Degree Of Protection	IP54 IEC 60529 plinth type open bottom)
Ik Degree Of Protection	IK10 IEC 62262 plain door)
Fire Resistance	1760 °F (960 °C) IEC 62208
Ambient Air Temperature For Storage	-31194 °F (-3590 °C)

# Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480775901
Returnability	No
Country Of Origin	ES

## **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	32.09 in (81.5 cm)
Package 1 Width	50.39 in (128.0 cm)
Package 1 Length	17.72 in (45.0 cm)
Package 1 Weight	102.15 lb(US) (46.334 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	4
Package 2 Height	50.79 in (129 cm)
Package 2 Width	39.37 in (100 cm)
Package 2 Length	68.50 in (174 cm)
Package 2 Weight	339.51 lb(US) (154 kg)



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations