Product data sheet

Specifications





Floor standing polyester enclosure, Thalassa PLA, open bottom, ventilated canopy, 1250x1250x320mm, IP44, IK10

NSYPLAZT12123G

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1,865.39 USD

Main

Thalassa
Thalassa PLA
Multi-purpose
Suitable enclosure
PLAZT
49.21 in (1250 mm)
49.21 in (1250 mm)
12.60 in (320 mm)
Floor-standing
1 top part 1 bottom part 2 side part 2 door 2 rear panel 1 canopy 1 plinth

Complementary

Body Type	Open top and bottom part assembled with side parts
Door Type	Solid front
Number Of Doors	2
Door Opening Side	Right and left 180 °)
Lock Type	4 points lock, handle with 5 mm double bar insert
Accessibility For Operation	Bottom Front Rear Top
Removable Parts	Door by hinges Rear panel by fixing element Canopy by fixing element
Material	polyester reinforced with fibreglass
Color	Gray RAL 7035)
Standards	IEC 62208
Product Certifications	Veritas

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Electrical Insulation Class

Class II

Ip Degree Of Protection	IP44 IEC 60529 with plinth type open bottom part and ventilated canopy)
Ik Degree Of Protection	IK10 IEC 62262 plain door)
Fire Resistance	1760 °F (960 °C) IEC 62208
Ambient Air Temperature For Storage	-31194 °F (-3590 °C)

Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480776052
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	50.79 in (129.0 cm)
Package 1 Width	50.39 in (128.0 cm)
Package 1 Length	14.96 in (38.0 cm)
Package 1 Weight	134.07 lb(US) (60.813 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	2
Package 2 Height	50.00 in (127 cm)
Package 2 Width	39.37 in (100 cm)
Package 2 Length	60.24 in (153 cm)
Package 2 Weight	304.24 lb(US) (138 kg)

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations