Product data sheet

Specification





Floor standing polyester enclosure, Thalassa PLA, open bottom, ventilated canopy, 1250x1250x620mm, IP44, IK10

NSYPLAZT12126G

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 2,590.23 USD

Main

Range	Thalassa
Product Name	Thalassa PLA
Enclosure Type	Multi-purpose
Product Or Component Type	Suitable enclosure
Version	PLAZT
Nominal Height	49.21 in (1250 mm)
Nominal Width	49.21 in (1250 mm)
Nominal Depth	24.41 in (620 mm)
Enclosure Mounting	Floor-standing
Device Composition	1 top part 1 bottom part 2 side part 2 door 2 rear panel 1 canopy 1 plinth

Complementary

Body Type	Open top and bottom part assembled with side parts
Door Type	Solid front
Number Of Doors	2
Door Opening Side	Right and left 180 °)
Lock Type	4 points lock, handle with 5 mm double bar insert
Accessibility For Operation	Rear Top Front Bottom
Removable Parts	Door by hinges Rear panel by fixing element Canopy by fixing element
	polyester reinforced with fibreglass
Color	Gray RAL 7035)
Standards	IEC 62208
Product Certifications	Veritas

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Electrical Insulation Class Class II

Environment

Ip Degree Of Protection	IP44 IEC 60529 with plinth type open bottom part and ventilated canopy)
Ik Degree Of Protection	IK10 IEC 62262 plain door)
Fire Resistance	1760 °F (960 °C) IEC 62208
Ambient Air Temperature For Storage	-31194 °F (-3590 °C)

Ordering and shipping details

Category	US10ES180035
Discount Schedule	0ES1
Gtin	3606480772887
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	51.18 in (130.0 cm)
Package 1 Width	26.77 in (68.0 cm)
Package 1 Length	50.39 in (128.0 cm)
Package 1 Weight	167.55 lb(US) (76.0 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations