



Price\*\* : 1,929.88 USD



## Main

Range	Thalassa
Product name	Thalassa PLA
Enclosure type	Multi-purpose
Product or component type	Suitable enclosure
Version	PLAZT
Nominal height	59.06 in (1500 mm)
Nominal width	49.21 in (1250 mm)
Nominal depth	12.6 in (320 mm)
Enclosure mounting	Floor-standing
Device composition	1 top part 1 bottom part 1 canopy 2 rear panel 2 door 1 plinth 2 side part

## Complementary

Body type	Open top and bottom part assembled with side parts
Door type	Plain front
Number of doors	2
Door opening side	Right and left 180 °
Lock type	4 points lock, handle with 5 mm double bar insert
Accessibility for operation	Rear Front Top Bottom
Removable parts	Door by hinges Rear panel by fixing element

## Canopy by fixing element

Material	Polyester reinforced with fibreglass
Colour	Grey RAL 7035
Standards	IEC 62208
Product certifications	Veritas

## Environment

IP degree of protection	IP44 with plinth type open bottom part and ventilated canopy IEC 60529
IK degree of protection	IK10 plain door IEC 62262
Fire resistance	1760 °F (960 °C) IEC 62208
Ambient air temperature for storage	-31...194 °F (-35...90 °C)

## Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	003606480776137
Nbr. of units in pkg.	1
Package weight(Lbs)	59.53999999999999
Returnability	N
Country of origin	ES

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1511 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations