## **Product data sheet**

Specification





Wall mounted polyester enclosure, Thalassa PLM, plain door, with metallic plate, 308x255x160mm, IP66, IK10, RAL 7035

NSYPLM3025PG

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 150.00 USD

### Main

Range	Thalassa
Product Name	Thalassa PLM
Device Short Name	PLM
Enclosure Type	Multi-purpose
Category	Compact enclosure
Nominal Height	12.13 in (308 mm)
Nominal Width	10.04 in (255 mm)
Nominal Depth	6.30 in (160 mm)
Enclosure Mounting	Wall mounted
<b>Device Composition</b>	1 body 1 door 1 mounting plate 1 lock
Door Type	Solid
Lock Type	3 mm double-bar lock

### Complementary

Number Of Locks	1
Mounting Plate Description	Plain steel
Accessibility For Operation	Front
Removable Parts	Door by hinges Mounting plate by fixing element
Material	polyester reinforced with fibreglass
Color	Gray RAL 7035)
Standards	NEMA classification 13 NEMA classification 4X IEC 62208
Product Certifications	UL
Electrical Insulation Class	Class II

### **Environment**

Ip Degree Of Protection IP66 IEC 60529

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ik Degree Of Protection	IK10 IEC 62262
Fire Resistance	1760 °F (960 °C) IEC 62208
Ambient Air Temperature For Operation	-40176 °F (-4080 °C)

# Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480776458
Returnability	No
Country Of Origin	ES

### **Packing Units**

9	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.24 in (26.0 cm)
Package 1 Width	7.09 in (18.0 cm)
Package 1 Length	12.99 in (33.0 cm)
Package 1 Weight	7.28 lb(US) (3.3 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	90
Package 2 Height	47.24 in (120 cm)
Package 2 Width	39.37 in (100 cm)
Package 2 Length	57.87 in (147 cm)
Package 2 Weight	765.00 lb(US) (347 kg)



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations