Product data sheet

Specifications





Wall mounted polyester enclosure, Thalassa PLM, glazed door, 530x430x200mm, IP66, IK08, RAL 7035

NSYPLM54TG

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 342.81 USD

Main

Range	Thalassa
Product Name	Thalassa PLM
Device Short Name	PLM
Enclosure Type	Multi-purpose
Category	Compact enclosure
Nominal Height	20.87 in (530 mm)
Nominal Width	16.93 in (430 mm)
Nominal Depth	7.87 in (200 mm)
Enclosure Mounting	Wall mounted
Device Composition	1 body 1 door 2 lock
Door Type	Transparent
Lock Type	3 mm double-bar lock

Complementary

Number Of Locks	2
Mounting Plate Description	Without mounting plate
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	Body polyester reinforced with fibreglass Door tempered glass
Color	Gray RAL 7035)
Standards	NEMA classification 13 NEMA classification 4X IEC 62208
Product Certifications	UL
Electrical Insulation Class	Class II

Environment

Ip Degree Of Protection IP66 IEC 60529

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ik Degree Of Protection	IK08 IEC 62262
Fire Resistance	1760 °F (960 °C) IEC 62208
Ambient Air Temperature For Operation	-40176 °F (-4080 °C)

Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480776601
Returnability	No
Country Of Origin	ES

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.06 in (23.000 cm)
Package 1 Width	18.11 in (46.000 cm)
Package 1 Length	23.23 in (59.000 cm)
Package 1 Weight	17.24 lb(US) (7.820 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	5
Package 2 Height	17.72 in (45.000 cm)
Package 2 Width	39.37 in (100.000 cm)
Package 2 Length	47.24 in (120.000 cm)
Package 2 Weight	114.86 lb(US) (52.100 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations