Product data sheet

Specification





Wall mounted polyester enclosure, Thalassa PLM, glazed door, with handle, 530x430x200mm, IP66, IK08, RAL 7035

NSYPLM54TVG

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 395.27 USD

Main

Range	Thalassa
Product Name	Thalassa PLM
Device Short Name	PLM
Enclosure Type	Multi-purpose
Category	Compact enclosure
Nominal Height	20.87 in (530 mm)
Nominal Width	16.93 in (430 mm)
Nominal Depth	7.87 in (200 mm)
Enclosure Mounting	Wall mounted
Device Composition	1 body 1 door 1 handle lock
Door Type	Transparent
Lock Type	3 points lock, handle with 1242E key lock

Complementary

Number Of Locks	1
Mounting Plate Description	Without mounting plate
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	Body polyester reinforced with fibreglass Door tempered glass
Color	Gray RAL 7035)
Standards	NEMA classification 4X NEMA classification 13 IEC 62208
Product Certifications	UL
Electrical Insulation Class	Class II

Environment

Ip Degree Of Protection IP66 IEC 60529

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ik Degree Of Protection	IK08 IEC 62262
Fire Resistance	1760 °F (960 °C) IEC 62208
Ambient Air Temperature For Operation	-40176 °F (-4080 °C)

Ordering and shipping details

	• • •
Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480776618
Returnability	No
Country Of Origin	ES

Packing Units

PCE
1
17.72 in (45.0 cm)
9.06 in (23.0 cm)
22.05 in (56.0 cm)
19.85 lb(US) (9.003 kg)
PAM
30
47.24 in (120 cm)
39.37 in (100 cm)
75.98 in (193 cm)
628.32 lb(US) (285 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations