

# Product data sheet

## Characteristics

# NSYPLM54VG

wall-mounting enclosure polyester monobloc IP66  
H530xW430xD200mm 3points lock

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 324.42 USD



### Main

Range	Thalassa
Product name	Thalassa PLM
Device short name	PLM
Enclosure type	Multi-purpose
Category	Compact enclosure
Nominal height	20.87 in (530 mm)
Nominal width	16.93 in (430 mm)
Nominal depth	7.87 in (200 mm)
Enclosure mounting	Wall mounted
Device composition	Door 1 Body 1 Handle lock 1
Body type	One piece moulded with notches in the rear Built-in canopy
Door type	Plain
Lock type	3 points lock, handle with 1242E key lock

### Complementary

Number of locks	2
Mounting plate description	Without mounting plate
Accessibility for operation	Front
Removable parts	Door by hinges
Material	Polyester reinforced with fibreglass
Colour	Grey RAL 7035
Standards	IEC 62208 NEMA classification 13 NEMA classification 4X

Product certifications	UL
------------------------	----

## Environment

IP degree of protection	IP66 IEC 60529
IK degree of protection	IK10 IEC 62262
Fire resistance	1760 °F (960 °C) IEC 62208
Ambient air temperature for storage	-31...194 °F (-35...90 °C)

## Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	003606480776625
Nbr. of units in pkg.	1
Package weight(Lbs)	17.690000000000001
Returnability	N
Country of origin	ES

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations