Product data sheet

Specifications





Wall mounted polyester enclosure, Thalassa PLM, plain door, with bakelite plate, 647x436x250mm, IP66, IK10, RAL 7035

NSYPLM64BG

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 272.56 USD

Main

| Range | Thalassa |
|--------------------|--|
| Product Name | Thalassa PLM |
| Device Short Name | PLM |
| Enclosure Type | Multi-purpose |
| Category | Compact enclosure |
| Nominal Height | 25.47 in (647 mm) |
| Nominal Width | 17.17 in (436 mm) |
| Nominal Depth | 9.84 in (250 mm) |
| Enclosure Mounting | Wall mounted |
| Device Composition | 1 body 1 door 1 mounting plate 2 lock |
| Door Type | Solid |
| Lock Type | 3 mm double-bar lock |
| | |

Complementary

| Number Of Locks | 2 |
|-----------------------------|---|
| Mounting Plate Description | Plain bakelite |
| Accessibility For Operation | Front |
| Removable Parts | Door by hinges Mounting plate by fixing element |
| Material | polyester reinforced with fibreglass |
| Color | Gray RAL 7035) |
| Standards | NEMA classification 13 IEC 62208 NEMA classification 4X |
| Product Certifications | UL |
| Electrical Insulation Class | Class II |

Environment

Ip Degree Of Protection

IP66 IEC 60529

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Ik Degree Of Protection | IK10 IEC 62262 |
|--|----------------------------|
| Fire Resistance | 1760 °F (960 °C) IEC 62208 |
| Ambient Air Temperature For Operation | -40176 °F (-4080 °C) |

Ordering and shipping details

| Category | US10ES180034 |
|-------------------|---------------|
| Discount Schedule | 0ES1 |
| Gtin | 3606480776649 |
| Returnability | No |
| Country Of Origin | ES |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|------------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 17.72 in (45.0 cm) |
| Package 1 Width | 10.83 in (27.5 cm) |
| Package 1 Length | 26.77 in (68.0 cm) |
| Package 1 Weight | 24.47 lb(US) (11.1 kg) |
| Unit Type Of Package 2 | РАМ |
| Number Of Units In Package 2 | 21 |
| Package 2 Height | 47.24 in (120 cm) |
| Package 2 Width | 39.37 in (100 cm) |
| Package 2 Length | 79.13 in (201 cm) |
| Package 2 Weight | 571.00 lb(US) (259 kg) |

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |