

NSYPLM64VG

wall-mounting enclosure polyester monobloc IP66
H647xW436xD250mm 3points lock

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 379.15 USD



Main

Range	Thalassa
Product name	Thalassa PLM
Device short name	PLM
Enclosure type	Multi-purpose
Category	Compact enclosure
Nominal height	25.47 in (647 mm)
Nominal width	17.17 in (436 mm)
Nominal depth	9.84 in (250 mm)
Enclosure mounting	Wall mounted
Device composition	1 body 1 door 1 handle lock
Body type	One piece moulded with notches in the rear Built-in canopy
Door type	Plain
Lock type	3 points lock, handle with 1242E key lock

Complementary

Number of locks	2
Mounting plate description	Without mounting plate
Accessibility for operation	Front
Removable parts	Door by hinges
Material	polyester reinforced with fibreglass
Color	grey RAL 7035)
Standards	NEMA classification 4X NEMA classification 13 IEC 62208

Product certifications	UL
------------------------	----

Environment

IP degree of protection	IP66 IEC 60529
IK degree of protection	IK10 IEC 62262
Fire resistance	1760 °F (960 °C) IEC 62208
Ambient air temperature for storage	-31...194 °F (-35...90 °C)

Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	03606480776687
Package weight(Lbs)	11.48 kg (25.3 lb(US))
Returnability	No
Country of origin	ES

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations