

Product data sheet

Characteristics

NSYPLS2736AG

PLS box, polyester rear, transparent PC cover
IP65 27x36x23cm

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 82.44 USD



Main

Range	Thalassa
Product name	Thalassa PLS
Device short name	PLS
Enclosure type	Multi-purpose
Category	Insulating modular box
Nominal height	10.63 in (270 mm)
Nominal width	14.17 in (360 mm)
Nominal depth	9.06 in (230 mm)
Enclosure mounting	Wall mounted
Device composition	Cover 1 on enclosure Locking screws Rear part 1 on enclosure
Body type	One piece moulded
Type of front cover	High transparent cover
Lock type	Slot screw

Complementary

Removable parts	Cover locking screw
Material	Polycarbonate cover Polyester reinforced with fibreglass rear
Colour	Grey RAL 7035 body
Standards	NEMA 4X NEMA classification 13 IEC 62208
Product certifications	UL

Environment

Electrical insulation class	Class II
IP degree of protection	IP65 IEC 60529
IK degree of protection	IK09 IEC 62262
Fire resistance	1760 °F (960 °C) IEC 62208
Ambient air temperature for storage	-22...158 °F (-30...70 °C)

Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	003606480776885
Nbr. of units in pkg.	1
Package weight(Lbs)	40.920000000000002
Returnability	N
Country of origin	ES

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1511 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations