

# Product data sheet

## Characteristics

# NSYPLS2754G

PLS box, polyester rear, transparent PC cover  
IP65 27x54x18cm

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 96.55 USD



### Main

Range	Thalassa
Product name	Thalassa PLS
Device short name	PLS
Enclosure type	Multi-purpose
Category	Insulating modular box
Nominal height	10.63 in (270 mm)
Nominal width	21.26 in (540 mm)
Nominal depth	7.09 in (180 mm)
Enclosure mounting	Wall mounted
Device composition	Cover 1 on enclosure Locking screws Rear part 1 on enclosure
Body type	One piece moulded
Type of front cover	Low transparent cover
Lock type	Slot screw

### Complementary

Removable parts	Cover locking screw
Material	Polycarbonate cover Polyester reinforced with fibreglass rear
Colour	Grey RAL 7035 body
Standards	NEMA classification 13 IEC 62208 NEMA 4X
Product certifications	UL

## Environment

Electrical insulation class	Class II
IP degree of protection	IP65 IEC 60529
IK degree of protection	IK09 IEC 62262
Fire resistance	1760 °F (960 °C) IEC 62208
Ambient air temperature for storage	-22...158 °F (-30...70 °C)

## Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	003606480776915
Nbr. of units in pkg.	1
Package weight(Lbs)	40.920000000000002
Returnability	N
Country of origin	ES

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1511 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations