

Product data sheet

Specifications



PLS box, polyester rear, opaque PC cover IP65 36x54x18cm

NSYPLSC3654

⚠ Discontinued on: Dec 2, 2020

⚠ End-of-service on: Dec 31, 2020

⚠ Discontinued

Main

Range	Thalassa
Product Name	Thalassa PLS
Device Short Name	PLS
Enclosure Type	Multi-purpose
Category	Insulating modular box
Nominal Height	14.17 in (360 mm)
Nominal Width	21.26 in (540 mm)
Nominal Depth	7.09 in (180 mm)
Enclosure Mounting	Wall mounted
Device Composition	1 cover on enclosure 1 rear part on enclosure locking screws
Body Type	One piece moulded
Type Of Front Cover	Low plain cover
Lock Type	Slot screw

Complementary

Removable Parts	Cover locking screw
Material	Cover polycarbonate Rear polyester reinforced with fibreglass
Color	Body Gray RAL 7032)
Standards	IEC 62208 NEMA 4X NEMA classification 13
Product Certifications	UL

Environment

Electrical Insulation Class	Class II
Ip Degree Of Protection	IP65 IEC 60529
Ik Degree Of Protection	IK09 IEC 62262
Fire Resistance	1760 °F (960 °C) IEC 62208
Ambient Air Temperature For Storage	-22...248 °F (-30...120 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Category	80036-ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
Gtin	3606480189067
Returnability	No
Country Of Origin	ES

Contractual warranty

Warranty	18 months
----------	-----------