

Product data sheet

Specifications



KIT FLUSH-MOUNTING POUR ATV T3

NSYPTDS3

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 525.60 USD

Main

Range	Spacial
Product Or Component Type	Drive flush mounting kit
Accessory Category	Mounting and fixing accessory
Product Specific Application	Process and utilities
Range Compatibility	Altivar variable speed drive ATV630 Altivar variable speed drive ATV930 Spacial SF and SM enclosures 23.62 in (600 mm) x 11.81 in (300 mm) Spacial S3D enclosure 23.62 in (600 mm) x 11.81 in (300 mm)
Compatibility For Altivar Process 630-930, Size:	3
Motor Power Kw	7.5 kW 220/240 V 11 kW 220/240 V 15 kW 380/480 V 18.5 kW 380/480 V 22 kW 380/480 V
Mounting Location	1 back of enclosure mounting plate 2 inside enclosure
Kit Composition	1 x mounting plate with flanges and integrated gasket, steel with anti-corrosive coating by screws and nuts 1 x fixing accessories 1 x drilling template 1 x instruction sheet 1 x edge protector profile, plastic

Complementary

Permanent Permissible Load	31.53 lb(US) (14.3 kg)
Color	Gray RAL 7035)
Height	External: 21.85 in (555 mm) Cut-out: 19.80 in (503 mm)
Width	External: 11.61 in (295 mm) Cut-out: 9.84 in (250 mm)
Depth	Wall-enclosure separation : 0.87 in (22 mm)
Net Weight	5.41 lb(US) (2.452 kg)
Services	Configuration of enclosure pre-drilled back Factory installation drive flush mounting kit

Environment

Ip Degree Of Protection	IP55 conforming to IEC 60529
-------------------------	------------------------------

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Category	US1CP4E22277
Discount Schedule	CP4E
Gtin	3606485433226
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.97 in (5 cm)
Package 1 Width	14.57 in (37 cm)
Package 1 Length	22.44 in (57 cm)
Package 1 Weight	5.41 lb(US) (2.452 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	30
Package 2 Height	19.69 in (50 cm)
Package 2 Width	39.37 in (100 cm)
Package 2 Length	47.24 in (120 cm)
Package 2 Weight	191.80 lb(US) (87 kg)

Sustainability



Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.