



# Spacial SF-E rear cable guide support - steel - zinc coated - 150 mm

NSYRCSUP15

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 88.08 USD

#### Main

Range	Spacial
Accessory / Separate Part Category	Cabling accessory
Product Or Component Type	Cable guide
Application	Electronic application Multi-purpose
Mounting Location	Rear of swing rack
Range Compatibility	Spacial Spacial SF Spacial Spacial SM
Device Composition	fixing elements 1 crossbar 2 cable guide support
Quantity Per Set	Set of 1

### Complementary

Material	steel	
Surface Finish	Zinc coated	
Fixing Mode	Clip-on - 19" rack profile	
Adjustment	Adjustable in height every 44.45 mm	
Height	1.18 in (30 mm)  Nominal 23.62 in (600 mm)	
Width		
Depth	5.91 in (150 mm)	

#### Ordering and shipping details

Category	US10ES180036	
Discount Schedule	0ES1	
Gtin	3606480067112	
Returnability	No	
Country Of Origin	ES	

#### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	1.38 in (3.5 cm)	
Package 1 Width	3.94 in (10.0 cm)	
Package 1 Length	22.44 in (57.0 cm)	
Package 1 Weight	19.68 oz (558.0 g)	
Unit Type Of Package 2	PAM	
Number Of Units In Package 2	500	
Package 2 Height	39.37 in (100.0 cm)	
Package 2 Width	39.37 in (100.0 cm)	
Package 2 Length	47.24 in (120.0 cm)	
Package 2 Weight	639.34 lb(US) (290.0 kg)	

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations