Product data sheet

Specification





Spacial SF 19" swing rack - 2200x800 mm - 45 modules

NSYRSWC45

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 996.85 USD

Main

| Range | Spacial |
|------------------------------------|---|
| Accessory / Separate Part Category | Mounting accessory |
| Product Or Component Type | 19" rack |
| Application | Electronic application |
| For Enclosure Nominal Dimensions | - H: 86.61 in (2200 mm) |
| Rack Type | Swing centred |
| Mounting Location | On structure of enclosure |
| Range Compatibility | Spacial Spacial SF Spacial Spacial SM |
| Device Composition | fixing elements 2 800 mm swing rack supports 1 19" swing rack 2 side plates with ball-lock handle |
| Quantity Per Set | Set of 1 |
| Number Of Units 19" | 45 |

Complementary

| • | |
|-------------------------------|---|
| Material | steel |
| Enclosure/Cubicle Description | Floor-standing enclosure |
| Surface Finish | Zinc coated |
| Lock Type | Handle with ball lock |
| Fixing Mode | By fixing element |
| Adjustment | Adjustable in depth every 25 mm |
| Color | Side plate Gray RAL 7035) |
| Permanent Permissible Load | 8.27 lb(US) (3.75 kg) per unit with a maximum of 150 kg |
| Opening Of The 19" Racks | Reversible 120 ° |
| Height | 86.61 in (2200 mm) |
| Width | 31.50 in (800 mm) |
| Depth | 82.72 in (2101 mm) |

Ordering and shipping details

| Category | US10ES180036 |
|-------------------|--------------|
| Discount Schedule | 0ES1 |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Gtin | 3606480067143 |
|-------------------|---------------|
| Returnability | No |
| Country Of Origin | US |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|------------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 4.33 in (11.0 cm) |
| Package 1 Width | 28.74 in (73.0 cm) |
| Package 1 Length | 82.72 in (210.1 cm) |
| Package 1 Weight | 68.34 lb(US) (31.0 kg) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |