Product data sheet

Specification





Spacial SF/SM partial 19" swing rack - 355 mm

NSYRSWP6

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1,083.82 USD

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	19" rack
Application	Electronic application
For Enclosure Nominal Dimensions	- H: 13.98 in (355 mm)
Rack Type	Partial swing
Mounting Location	Front of enclosure
Mounting Support	Partial 19" swing rack support
Range Compatibility	Spacial Spacial SF Spacial Spacial SM
Device Composition	1 rack
Number Of Units 19"	6

Complementary

Material	steel
Enclosure/Cubicle Description	Floor-standing enclosure
Surface Finish	Zinc coated
Lock Type	Lock 5 mm double bar
Fixing Mode	By fixing element
Adjustment	Adjustable in depth every 25 mm
Permanent Permissible Load	4.41 lb(US) (2 kg) per unit
Opening Of The 19" Racks	Reversible 120 °
Height	13.98 in (355 mm)
Width	23.62 in (600 mm)
Depth	13.19 in (335 mm)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480067327
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin ES

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.95 in (7.5 cm)
Package 1 Width	13.58 in (34.5 cm)
Package 1 Length	20.47 in (52.0 cm)
Package 1 Weight	5.56 lb(US) (2.522 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	25
Package 2 Height	19.69 in (50.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	209.44 lb(US) (95.0 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations