Product data sheet





HMI encl. Spacial S3CM. H800xW600xD300IP54 IK10, RAL7035.Rear door.

NSYS3CM806030

! Discontinued on: Dec 31, 2023

① To be discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1,305.97 USD

Main

Range	Spacial
Product Name	Spacial S3CM
Application	Human-machine dialogue application
Category	Control enclosure
Enclosure Nominal Height	31.50 in (800 mm)
Enclosure Nominal Width	23.62 in (600 mm)
Enclosure Nominal Depth	11.81 in (300 mm)
Installation Accessory Type	Suspension system
Product Destination	Interface
Device Composition	body door with lock rail reinforcement plate front trim frame cable gland plate

Complementary

Body Type	Single piece body
Door Type	Solid
Number Of Doors	Rear 1
Door Opening Side	Reversible 120 °)
Lock Type	3 mm double-bar lock
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Standard
Accessibility For Operation	Rear
Removable Parts	Door by hinges Trim frame by screws 2 rails by screws Cable gland plate by screws
Material	Enclosure and front face steel Trim frame aluminium
Surface Finish	epoxy-polyester powder

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Color	Enclosure Gray RAL 7035) Front face Gray RAL 7040)	
Net Weight	64.17 lb(US) (29.106 kg)	

Environment

Ip Degree Of Protection	IP54 IEC 60529
Ik Degree Of Protection	IK10 IEC 62262

Ordering and shipping details

Category	US10ES180033
Discount Schedule	0ES1
Gtin	3606480212871
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	32.28 in (82.0 cm)
Package 1 Width	24.41 in (62.0 cm)
Package 1 Length	12.60 in (32.0 cm)
Package 1 Weight	64.17 lb(US) (29.106 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations