

Product data sheet

Characteristics

NSYS3D101030D

Spacial S3D db plain door w/o
mount.plate.H1000xW1000xD300 IP 55 IK 10
RAL7035.

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 484.06 USD



Main

Range	Spacial
Product name	Spacial S3D
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	39.37 in (1000 mm)
Enclosure nominal width	39.37 in (1000 mm)
Enclosure nominal depth	11.81 in (300 mm)
Door type	Plain
Mounting plate description	Without mounting plate
Type of gland plate	Standard
Installation accessory type	Wall-mounting
Device composition	1 body 2 cable gland plate 1 lock 2 door

Complementary

Body type	Gutter-shaped front rail double sheet thickness Single piece body
Number of doors	Front face 2
Door opening side	Reversible 120 °)
Lock type	3 points lock, 3 mm double-bar
Accessibility for operation	Front
Removable parts	Door by hinges Cable gland plate by screws
Material	steel

Surface finish	epoxy-polyester powder
Color	grey RAL 7035)
Standards	IEC 62208
Product certifications	GL UL CUL LR BV DNV
Net weight	101.41 lb(US) (46 kg)

Environment

IP degree of protection	IP55 IEC 60529
IK degree of protection	IK10 IEC 62262

Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	03606480160332
Package weight(Lbs)	45.90 kg (101.2 lb(US))
Returnability	No
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: No which is known to the State of California to cause No harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------