# **Product data sheet**

Specifications





Wall mounted steel enclosure, Spacial S3D, double plain door, with mounting plate, 1200x1200x400mm, IP55, IK10

NSYS3D121240DP

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 1,586.87 USD

#### Main

Range	Spacial
Product Name	Spacial S3D
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	47.24 in (1200 mm)
Enclosure Nominal Width	47.24 in (1200 mm)
Enclosure Nominal Depth	15.75 in (400 mm)
Door Type	Solid
Mounting Plate Description	Plain
Type Of Gland Plate	Standard
Installation Accessory Type	Wall-mounting
Device Composition	1 body 2 cable gland plate 2 door with lock 1 mounting plate

### Complementary

Body Type	Single piece body Gutter-shaped front rail double sheet thickness
Number Of Doors	Front face 2
Door Opening Side	Reversible 120 °)
Lock Type	3 points lock, 3 mm double-bar
Accessibility For Operation	Front
Removable Parts	Door by hinges Cable gland plate by screws Mounting plate by fixing element
Material	Enclosure steel Mounting plate galvanised steel
Surface Finish	Enclosure epoxy-polyester powder
Color	Enclosure Gray RAL 7035)
Standards	IEC 62208

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Net Weight	246.92 lb(US) (112 kg)
	DNV cUL
	BV
	GL
	UL
Product Certifications	LR

### **Environment**

Ik Degree Of Protection	IK10 IEC 62262	
Ip Degree Of Protection	IP55 IEC 60529	

# Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480159954
Returnability	No
Country Of Origin	FR

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17.72 in (45.0 cm)
Package 1 Width	48.03 in (122.0 cm)
Package 1 Length	52.36 in (133.0 cm)
Package 1 Weight	246.92 lb(US) (112.0 kg)

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations