

Product data sheet

Characteristics

NSYS3D12830P

Spacial S3D plain door with mount.plate.
H1200xW800xD300 IP66 IK10 RAL7035.

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 545.76 USD



Main

| | |
|-----------------------------|---|
| Range | Spacial |
| Product name | Spacial S3D |
| Application | Multi-purpose |
| Category | Compact enclosure |
| Enclosure nominal height | 47.24 in (1200 mm) |
| Enclosure nominal width | 31.5 in (800 mm) |
| Enclosure nominal depth | 11.81 in (300 mm) |
| Door type | Plain |
| Mounting plate description | Plain |
| Type of gland plate | Standard |
| Installation accessory type | Wall-mounting |
| Device composition | Body 1 Cable gland plate 2 Mounting plate 1 Door with lock 1 |

Complementary

| | |
|-----------------------------|---|
| Body type | Single piece body Gutter-shaped front rail double sheet thickness |
| Number of doors | 1 front face |
| Door opening side | Reversible 120 ° |
| Lock type | 3 points lock, 3 mm double-bar |
| Accessibility for operation | Front |
| Removable parts | Door by hinges Cable gland plate by screws Mounting plate by fixing element |
| Material | Galvanised steel mounting plate Steel enclosure |

| | |
|------------------------|------------------------------------|
| Surface finish | Epoxy-polyester powder enclosure |
| Colour | Grey RAL 7035 enclosure: |
| Standards | IEC 62208 |
| Product certifications | UL DNV BV LR GL CUL |
| Product weight | 134.48 lb(US) (61 kg) |

Environment

| | |
|-------------------------|------------------------------|
| IP degree of protection | IP66 conforming to IEC 60529 |
| IK degree of protection | IK10 conforming to IEC 62262 |

Ordering and shipping details

| | |
|-----------------------|--|
| Category | 80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL |
| Discount Schedule | ES1 |
| GTIN | 003606480159879 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 134.19999999999999 |
| Returnability | N |
| Country of origin | FR |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 0810 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|