

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 143.41 USD



Main

Range	Spacial
Product name	Spacial S3DB
Application	Terminal application
Category	Compact enclosure
Enclosure nominal height	11.81 in (300 mm)
Enclosure nominal width	23.62 in (600 mm)
Enclosure nominal depth	5.91 in (150 mm)
Door type	Plain
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Installation accessory type	Wall-mounting Horizontal or vertical position
Product destination	For equipping with terminal
Device composition	Lock 1 Door 1 Body 1

Complementary

Body type	Gutter-shaped front rail double sheet thickness Single piece body
Number of doors	1 front face
Door opening side	Reversible 180 °
Lock type	3 mm double-bar lock
Accessibility for operation	Front
Removable parts	Door by hinges
Material	Steel
Surface finish	Epoxy-polyester powder

Colour	Grey RAL 7035
Standards	IEC 62208
Product certifications	GL DNV CUL BV LR UL
Product weight	9.88 kg

Environment

IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	003606480158766
Nbr. of units in pkg.	1
Package weight(Lbs)	21.740000000000002
Returnability	N
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0810 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------