Product data sheet

Specifications





Wall mounted steel enclosure, Spacial S3DC, plain door, without plain chasis, 600x400x250mm, IP66, IK10

NSYS3DC6425

Product availability: Stock - Normally stocked in distribution facility

Price*: 206.20 USD

Main

Range	Spacial
Product Name	Spacial S3DC
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	23.62 in (600 mm)
Enclosure Nominal Width	15.75 in (400 mm)
Enclosure Nominal Depth	9.84 in (250 mm)
Door Type	Solid
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Installation Accessory Type	Wall-mounting
Device Composition	1 body 1 door 1 lock

Complementary

Body Type	Single piece body Gutter-shaped front profile double sheet thickness
Number Of Doors	Front face 1
Door Opening Side	Reversible 120 °)
Lock Type	3 points lock, screw driver insert
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	steel
Surface Finish	epoxy-polyester powder
Color	Gray RAL 7035)
Standards	IEC 62208
Product Certifications	UL
Net Weight	26.46 lb(US) (12 kg)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Environment

Nema Degree Of Protection	NEMA 4X/13
Ik Degree Of Protection	IK10 IEC 62262
Ip Degree Of Protection	IP66 IEC 60529

Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480314087
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.20 in (31.0 cm)
Package 1 Width	16.93 in (43.0 cm)
Package 1 Length	27.17 in (69.0 cm)
Package 1 Weight	26.46 lb(US) (12.0 kg)
Unit Type Of Package 2	РАМ
Number Of Units In Package 2	16
Package 2 Height	73.23 in (186.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	458.56 lb(US) (208.0 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations