Product data sheet

Specifications





Spacial S3HF H400xW300xD200 EMC-immunity IP55 RAL7035

NSYS3HF4320P

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 635.76 USD

Main

Range	Spacial
Product Name	Spacial S3HF
Application	Industrial Application
Category	Compact enclosure
Enclosure Nominal Height	15.75 in (400 mm)
Enclosure Nominal Width	11.81 in (300 mm)
Enclosure Nominal Depth	7.87 in (200 mm)
Door Type	Solid
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Installation Accessory Type	Wall-mounting
Device Composition	1 body 1 door with lock 1 mounting plate

Complementary

Body Type	Single piece body
Number Of Doors	Front face 1
Lock Type	3 mm double-bar lock
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	Body aluzinc
Surface Finish	epoxy-polyester powder
Color	Gray RAL 7035)
Standards	IEC 60529
Net Weight	15.43 lb(US) (7 kg)

Environment

Electromagnetic Compatibility	EMC immunity
Ik Degree Of Protection	IK10 IEC 62262
Ip Degree Of Protection	IP55

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US10ES180035
Discount Schedule	0ES1
Gtin	3606480212840
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.75 in (40.0 cm)
Package 1 Width	11.81 in (30.0 cm)
Package 1 Length	7.87 in (20.0 cm)
Package 1 Weight	15.43 lb(US) (7.0 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations