

# Product data sheet

Specifications



## Spacial S3HF H800xW600xD300 EMC-immunity IP55 RAL7035

NSYS3HF8630P

Product availability: Non-Stock - Not normally stocked in distribution facility

**Price\*: 1,185.80 USD**

### Main

Range	Spacial
Product Name	Spacial S3HF
Application	Industrial Application
Category	Compact enclosure
Enclosure Nominal Height	31.50 in (800 mm)
Enclosure Nominal Width	23.62 in (600 mm)
Enclosure Nominal Depth	11.81 in (300 mm)
Door Type	Solid
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Installation Accessory Type	Wall-mounting
Device Composition	1 body 1 door with lock 1 mounting plate

### Complementary

Body Type	Single piece body
Number Of Doors	Front face 1
Lock Type	3 points lock, 3 mm double-bar
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	Body aluzinc
Surface Finish	epoxy-polyester powder
Color	Gray RAL 7035)
Standards	IEC 60529
Net Weight	70.55 lb(US) (32 kg)

### Environment

Electromagnetic Compatibility	EMC immunity
Ik Degree Of Protection	IK10 IEC 62262
Ip Degree Of Protection	IP55

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Ordering and shipping details

Category	US10ES180035
Discount Schedule	0ES1
Gtin	3606480212789
Returnability	No
Country Of Origin	ES

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	32.10 in (81.534 cm)
Package 1 Width	14.50 in (36.83 cm)
Package 1 Length	23.60 in (59.944 cm)
Package 1 Weight	69.84 lb(US) (31.679 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

Mercury Free

RoHS Exemption Information Yes

## Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu RoHS Directive Pro-active compliance (Product out of EU RoHS legal scope)

China RoHS Regulation [China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information.

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile No need of specific recycling operations