

# Product data sheet

## Characteristics

# NSYS3X101030H

## SPACIAL S3X stainless 316L, Scotch Brite® finish, H1000xW1000xD300 mm.

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 3,238.07 USD



### Main

Range	Spacial
Product name	Spacial S3X
Enclosure type	Multi-purpose
Category	Compact enclosure
Nominal height	39.37 in (1000 mm)
Nominal width	39.37 in (1000 mm)
Nominal depth	11.81 in (300 mm)
Product installation	Wall-mounting
Device composition	1 body 2 door 1 lock ( door ) 1 reinforcement frame drilled ( door )

### Complementary

Body type	Single piece body, cross-shaped structure Gutter shaped front rail
Door type	Plain
Number of doors	Front face: 2 door(s)
Door opening side	120 °, reversible
Lock type	3 points lock, 3 mm double-bar
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Accessibility for operation	Front
Removable parts	Door fixing: by hinges
Material	Hinge: stainless steel Body and door: stainless steel 316L
Surface finish	Body and door: Scotch-Brite® brushed

Thickness	0.06 in (1.5 mm)
Product weight	103.62 lb(US) (47 kg)

## Environment

Standards	IEC 62208
Product certifications	CAN/CSA 22 UL 508 type A
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Environmental characteristic	Corrosive Specific hygiene

## Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	003606480154959
Nbr. of units in pkg.	1
Package weight(Lbs)	103.40000000000001
Returnability	N
Country of origin	FR

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0810 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------