Product data sheet

Specification





Wall mounted enclosure, Spacial S3X, stainless steel 316L, double plain door, 1200x1000x300mm, IP55

NSYS3X121030H

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 3,576.18 USD

Main

Range	Spacial
Product Name	Spacial S3X
Enclosure Type	Multi-purpose
Category	Compact enclosure
Nominal Height	47.24 in (1200 mm)
Nominal Width	39.37 in (1000 mm)
Nominal Depth	11.81 in (300 mm)
Product Installation	Wall-mounting
Device Composition	1 body
	2 door
	1 lock door
	1 reinforcement frame drilled door

Complementary

Body Type	Single piece body, cross-shaped structure Gutter shaped front rail
Door Type	Solid
Number Of Doors	Front face 2
Door Opening Side	Reversible 120 °)
Lock Type	3 points lock, 3 mm double-bar
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	Hinge stainless steel Body and door stainless steel 316L
Surface Finish	Body and door Scotch-Brite® brushed
Net Weight	113.76 lb(US) (51.6 kg)

Environment

Standards IEC 62208

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	UL 508 type A CAN/CSA 22
Ip Degree Of Protection	IP55 IEC 60529
Ik Degree Of Protection	IK10 IEC 62262
Environmental Characteristic	Specific hygiene Corrosive

Ordering and shipping details

	-
Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480155000
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.60 in (32.0 cm)
Package 1 Width	39.96 in (101.5 cm)
Package 1 Length	48.03 in (122.0 cm)
Package 1 Weight	113.76 lb(US) (51.6 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	4
Package 2 Height	55.12 in (140.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	502.65 lb(US) (228.0 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations