

Product data sheet

Characteristics

NSYS3X12830H

SPACIAL S3X stainless 316L, Scotch Brite® finish, H1200xW800xD300 mm.

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 3,107.71 USD



Main

Range	Spacial
Product name	Spacial S3X
Enclosure type	Multi-purpose
Category	Compact enclosure
Nominal height	47.24 in (1200 mm)
Nominal width	31.5 in (800 mm)
Nominal depth	11.81 in (300 mm)
Product installation	Wall-mounting
Device composition	2 lock (door) 1 body 1 door 1 reinforcement frame drilled (door)

Complementary

Body type	Single piece body, cross-shaped structure Gutter shaped front rail
Door type	Plain
Number of doors	Front face: 1 door(s)
Door opening side	120 °, reversible
Lock type	2 points lock, 3 mm double-bar
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Accessibility for operation	Front
Removable parts	Door fixing: by hinges
Material	Lock: zamak Hinge: stainless steel Body and door: stainless steel 316L
Surface finish	Lock: chromium plated

Body and door: Scotch-Brite® brushed

Thickness	0.06 in (1.5 mm)
Product weight	97 lb(US) (44 kg)

Environment

Standards	IEC 62208
Product certifications	CAN/CSA 22 UL 508 type A
IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Environmental characteristic	Corrosive Specific hygiene

Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	003606480155024
Nbr. of units in pkg.	1
Package weight(Lbs)	99
Returnability	N
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0810 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------