# Product data sheet

Specification





Wall mounted enclosure, Spacial S3X, stainless steel 304L, plain door, 300x300x150mm, IP66

NSYS3X3315

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 290.05 USD

### Main

Range	Spacial
Product Name	Spacial S3X
Enclosure Type	Multi-purpose
Category	Compact enclosure
Nominal Height	11.81 in (300 mm)
Nominal Width	11.81 in (300 mm)
Nominal Depth	5.91 in (150 mm)
Product Installation	Wall-mounting
<b>Device Composition</b>	1 body 1 lock door 1 door

### Complementary

Body Type	Single piece body, cross-shaped structure Gutter shaped front rail
Door Type	Solid
Number Of Doors	Front face 1
Door Opening Side	Reversible 120 °)
Lock Type	3 mm double-bar lock
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	Body and door stainless steel 304L Lock zamak Hinge stainless steel
Surface Finish	Body and door Scotch-Brite® brushed Lock chromium plated
Net Weight	8.96 lb(US) (4.062 kg)

### **Environment**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	CAN/CSA 22 UL 508 type A
Ip Degree Of Protection	IP66 IEC 60529
Ik Degree Of Protection	IK10 IEC 62262
Environmental Characteristic	Corrosive Specific hygiene

# Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480155079
Returnability	No
Country Of Origin	BG

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.50 in (16.5 cm)
Package 1 Width	12.20 in (31.0 cm)
Package 1 Length	12.20 in (31.0 cm)
Package 1 Weight	8.73 lb(US) (3.961 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	126
Number Of Units In Package 2	126
Number Of Units In Package 2 Package 2 Height	126 47.24 in (120 cm)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations