Product data sheet

Specification





Wall mounted enclosure, Spacial S3X, stainless steel 304L, plain door, 400x300x200mm, IP66

NSYS3X4320

Product availability: Stock - Normally stocked in distribution

Price*: 376.48 USD

Main

Range	Spacial
Product Name	Spacial S3X
Enclosure Type	Multi-purpose
Category	Compact enclosure
Nominal Height	15.75 in (400 mm)
Nominal Width	11.81 in (300 mm)
Nominal Depth	7.87 in (200 mm)
Product Installation	Wall-mounting
Device Composition	1 body
	1 lock door
	1 door

Complementary

Body Type	Single piece body, cross-shaped structure Gutter shaped front rail
Door Type	Solid
Number Of Doors	Front face 1
Door Opening Side	Reversible 120 °)
Lock Type	3 mm double-bar lock
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	Body and door stainless steel 304L Lock zamak Hinge stainless steel
Surface Finish	Body and door Scotch-Brite® brushed Lock chromium plated
Net Weight	12.05 lb(US) (5.468 kg)

Environment

Standards	IEC 62208	
-----------	-----------	--

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	UL 508 type A CAN/CSA 22
Ip Degree Of Protection	IP66 IEC 60529
Ik Degree Of Protection	IK10 IEC 62262
Environmental Characteristic	Corrosive Specific hygiene

Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480155116
Returnability	Yes
Country Of Origin	BG

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.46 in (21.5 cm)
Package 1 Width	12.20 in (31.0 cm)
Package 1 Length	16.34 in (41.5 cm)
Package 1 Weight	12.05 lb(US) (5.468 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	64
Package 2 Height	70.87 in (180.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	834.67 lb(US) (378.6 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations