Product data sheet

Specifications





Wall mounted enclosure, Spacial S3X, stainless steel 304L, plain door, 800x600x250mm, IP66

NSYS3X8625

Product availability: Stock - Normally stocked in distribution facility

Price*: 895.80 USD

Main

Range	Spacial
Product Name	Spacial S3X
Enclosure Type	Multi-purpose
Category	Compact enclosure
Nominal Height	31.50 in (800 mm)
Nominal Width	23.62 in (600 mm)
Nominal Depth	9.84 in (250 mm)
Product Installation	Wall-mounting
Device Composition	1 body
	1 door
	2 lock door
	2 perforated vertical profile drilled door

Complementary

Body Type	Single piece body, cross-shaped structure Gutter shaped front rail
Door Type	Solid
Number Of Doors	Front face 1
Door Opening Side	Reversible 120 °)
Lock Type	2 points lock, 3 mm double-bar
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	Body and door stainless steel 304L Lock zamak Hinge stainless steel
Surface Finish	Body and door Scotch-Brite® brushed Lock chromium plated
Net Weight	49.55 lb(US) (22.474 kg)

Environment

Standards

IEC 62208

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Product Certifications	CAN/CSA 22 UL 508 type A
Ip Degree Of Protection	IP66 IEC 60529
Ik Degree Of Protection	IK10 IEC 62262
Environmental Characteristic	Specific hygiene Corrosive

Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480155291
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	32.28 in (81.99 cm)
Package 1 Width	24.21 in (61.49 cm)
Package 1 Length	10.63 in (27 cm)
Package 1 Weight	49.56 lb(US) (22.48 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	12
Package 2 Height	78.35 in (199 cm)
Package 2 Width	39.37 in (100 cm)
Package 2 Length	47.24 in (120 cm)
Package 2 Weight	653.67 lb(US) (296.5 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations