# **Product data sheet**

Specification





### Metal industrial box plain door H200xW200xD120 IP66 IK10 RAL 7035

NSYSBM202012

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 53.82 USD

#### Main

Range	Spacial	
Product Name	Spacial SBM	
Device Application	Multi-purpose	
Category	Industrial box	
Pevice Short Name SBM		
Enclosure Type Flat face box		
Enclosure Nominal Height	7.87 in (200 mm)	
Enclosure Nominal Width	7.87 in (200 mm)	
<b>Enclosure Nominal Depth</b>	4.72 in (120 mm)	
Enclosure Mounting	Wall mounted	
Device Composition	4 cover screw 1 cover 1 body	
Body Type	Single piece body folded and welded	
Type Of Front Cover	Plain door	
Cover Fixing	ring Half turn metal screw	
Lock Type	Captive screw PZ2 outside sealed area	
Removable Parts Cover by captive screws		

### Complementary

Material	sheet steel	
Surface Finish	Polyester powder	
Color	Gray RAL 7035)	
Standards	IEC 62208	
<b>Product Certifications</b>	LR DNV-GL UL BV	
Ip Degree Of Protection	IP66 IEC 60529	
Ik Degree Of Protection	IK10 conforming to IEC 62262	
Ambient Air Temperature For Storage	-31140 °F (-3560 °C)	
Operating Temperature	-31176 °F (-3580 °C)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

### Ordering and shipping details

Category	US10ES180033	
Discount Schedule	0ES1	
Gtin	3606480520143	
Returnability	No	
Country Of Origin	IN	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.51 in (14 cm)
Package 1 Width	8.66 in (22 cm)
Package 1 Length	8.66 in (22 cm)
Package 1 Weight	4.18 lb(US) (1.894 kg)
Unit Type Of Package 2	P12
Number Of Units In Package 2	124
Package 2 Height	41.34 in (105 cm)
Package 2 Width	31.50 in (80 cm)
Package 2 Length	47.24 in (120 cm)
Package 2 Weight	540.13 lb(US) (245 kg)

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations