Product data sheet

Specification





Metal industrial box plain door H200xW300xD80 IP66 IK10 RAL 7035

NSYSBM20308

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 67.68 USD

Main

Range	Spacial	
Product Name	Spacial SBM	
Device Application	ion Multi-purpose	
Category	Industrial box	
Device Short Name	SBM	
Enclosure Type	Flat face box	
Enclosure Nominal Height	7.87 in (200 mm)	
Enclosure Nominal Width	osure Nominal Width 11.81 in (300 mm)	
Enclosure Nominal Depth	3.15 in (80 mm)	
Enclosure Mounting	Wall mounted	
Device Composition	4 cover screw 1 cover 1 body	
Body Type	Single piece body folded and welded	
Type Of Front Cover	ront Cover Plain door	
Cover Fixing	Half turn metal screw	
Lock Type	Captive screw PZ2 outside sealed area	
Removable Parts	Cover by captive screws	

Complementary

Material	sheet steel	
Surface Finish	Polyester powder	
Color	Gray RAL 7035)	
Standards	IEC 62208	
Product Certifications	LR DNV-GL UL BV	
Ip Degree Of Protection	IP66 IEC 60529	
Ik Degree Of Protection	Protection IK10 conforming to IEC 62262	
Ambient Air Temperature For Storage	-31140 °F (-3560 °C)	
Operating Temperature	-31176 °F (-3580 °C)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US10ES180033	
Discount Schedule	0ES1	
Gtin	3606480520068	
Returnability	No	
Country Of Origin	IN	

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	3.74 in (9.5 cm)	
Package 1 Width	8.46 in (21.5 cm)	
Package 1 Length	12.40 in (31.5 cm)	
Package 1 Weight	4.69 lb(US) (2.128 kg)	
Unit Type Of Package 2	P12	
Number Of Units In Package 2	112	
Package 2 Height	41.34 in (105.0 cm)	
Package 2 Width	ge 2 Width 31.50 in (80.0 cm)	
Package 2 Length	47.24 in (120.0 cm)	
Package 2 Weight	548.95 lb(US) (249.0 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations