Product data sheet

Specification





Metal industrial box FL21 cable entry H300xW600xD120 IP55 IK10 RAL 7035

NSYSBMC306012

! Discontinued on: Jan 23, 2021

(!) Discontinued

Main

| Range | Spacial | |
|--------------------------------|---|--|
| Product Name | Spacial SBM | |
| Device Application | Multi-purpose | |
| Category | Industrial box | |
| Device Short Name | SBMC | |
| Enclosure Type | Entry box | |
| Enclosure Nominal Height | 11.81 in (300 mm) | |
| Enclosure Nominal Width | 23.62 in (600 mm) | |
| Enclosure Nominal Depth | 4.72 in (120 mm) | |
| Enclosure Mounting | Wall mounted | |
| Device Composition | 1 cover 1 body 6 cover screw 6 FL21 cable gland plate | |
| Body Type | Single piece body folded and welded | |
| Type Of Front Cover | Plain door | |
| Cover Fixing | Half turn metal screw | |
| Lock Type | Captive screw PZ2 outside sealed area | |
| Removable Parts | Cover by captive screws Cable gland plate screw | |

Complementary

| Material | sheet steel | |
|-------------------------------------|------------------------------|--|
| Surface Finish | Polyester powder | |
| Color | Gray RAL 7035) | |
| Standards | IEC 62208 | |
| Product Certifications | LR UL GL BV DNV | |
| Ip Degree Of Protection | IP55 IEC 60529 | |
| Ik Degree Of Protection | IK10 conforming to IEC 62262 | |
| Ambient Air Temperature For Storage | -31140 °F (-3560 °C) | |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Operating Temperature | -31176 °F (-3580 °C) |
|-----------------------|-------------------------|
| Net Weight | 19.06 lb(US) (8.644 kg) |

Ordering and shipping details

| Category | 80033-ENCLOSURE SYSTEMS POLYESTER | |
|-------------------|-----------------------------------|--|
| Discount Schedule | ES1 | |
| Gtin | 3606480520372 | |
| Returnability | No | |
| Country Of Origin | IN | |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-------------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 24.41 in (62 cm) |
| Package 1 Width | 12.99 in (33 cm) |
| Package 1 Length | 5.91 in (15 cm) |
| Package 1 Weight | 19.06 lb(US) (8.644 kg) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ② | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| ⊘ | Toxic Heavy Metal Free | |
| ⊘ | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |