

# Product data sheet

Specifications



## Spacial S24 - industrial box - 182x167x107 - plain door

NSYSBS18169F

⚠ Discontinued on: Dec 2, 2020

⚠ End-of-service on: Dec 31, 2020

⚠ Discontinued

### Main

Range	Spacial S24
Device Application	Safety and alarm system
Product Or Component Type	Industrial box
Height	7.17 in (182 mm)
Width	6.57 in (167 mm)
Depth	4.21 in (107 mm)
Internal Height	7.09 in (180 mm)
Internal Width	6.50 in (165 mm)
Internal Depth	3.78 in (96 mm)
Enclosure Mounting	Surface
Device Composition	4 nut M6 x 8 grounding screw
Type Of Front Cover	Plain door
Lock Type	By screws

### Complementary

Material	steel
Surface Finish	Epoxy-polyester powder
Color	Gray RAL 7035)
Electrical Insulation Class	Class II
Ip Degree Of Protection	IP55 IEC 60529
Ik Degree Of Protection	IK07
Environmental Characteristic	UV resistant Corrosion resistance

### Ordering and shipping details

Category	80033-ENCLOSURE SYSTEMS POLYESTER
Discount Schedule	ES1
Gtin	03606480188091
Returnability	No
Country Of Origin	FR

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------