

# Product data sheet

Specifications



## Spacial S24 - industrial box - 332x212x137 - door with window

NSYSBS232112FT

⚠ Discontinued on: Dec 2, 2020

⚠ End-of-service on: Dec 31, 2020

⚠ Discontinued

### Main

Range	Spacial S24
Device Application	Safety and alarm system
Product Or Component Type	Industrial box
Height	9.13 in (232 mm)
Width	8.35 in (212 mm)
Depth	5.39 in (137 mm)
Internal Height	9.06 in (230 mm)
Internal Width	8.27 in (210 mm)
Internal Depth	4.96 in (126 mm)
Enclosure Mounting	Surface
Device Composition	4 nut M6 x 8 grounding screw
Type Of Front Cover	Door with window
Lock Type	By screws

### Complementary

Material	steel
Surface Finish	Epoxy-polyester powder
Color	Gray RAL 7035)
Electrical Insulation Class	Class II
Ip Degree Of Protection	IP55 IEC 60529
Ik Degree Of Protection	IK07
Environmental Characteristic	UV resistant Corrosion resistance

### Ordering and shipping details

Category	80033-ENCLOSURE SYSTEMS POLYESTER
Discount Schedule	ES1
Gtin	03606480188176
Returnability	No
Country Of Origin	FR

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------