

Product data sheet

Characteristics

NSYSDRSDCR400

Set of 2 step slides made of treated steel,
D400mm and W1000 or W1200

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 133.88 USD



Main

Category	Mounting accessory
Product or component type	Step slide
Range compatibility	Spacial CRN Spacial S3D Spacial S3CM
Application	Multi-purpose
For enclosure nominal dimensions	-
Mounting location	Top and bottom middle of enclosure on central backstud
Product destination	2 mounting plates for enclosure width 1000 mm 2 mounting plates for enclosure width 1200 mm
Device composition	Fixing elements 2 sliding rails
Quantity per set	Set of 1
Material	Galvanised steel

Complementary

Fixing mode	By fixing element On backstuds (welded in the enclosure)
Adjustment	In depth of the plate or other accessories in steps of 12.5 mm
Depth	Nominal: 15.75 in (400 mm)
Product weight	1.19 lb(US) (0.54 kg)

Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	003606480184413
Nbr. of units in pkg.	1

Package weight(Lbs)	1.1899999999999999
Returnability	N
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------